


APQ 200/1600 Fluorite Quadruplet Polychromat

APQ



APQ 200/1600 Fluorite Quadruplet Polychromat

Polychromatic top-of-the-line refractor for professional use. Making the invisible visible.

Features

- UBVRl Fluorite Quadruplet Polychromat
- Four lens aspherical design
- System correction by precision optics master
- CaF₂ lens protected between glass lenses
- Oil spaced without air gaps
- Ultra broad band antireflection coating
- Objective in compensation cell
- Objective adjustable
- Retractable and lockable dew cap
- Feather Touch Focuser FTF3545
- Depending on the observation task, the basic system is combined with the special field corrector, focal reducer corrector or Barlow system

Description

- The APQ 200/1600 Fluorite Quadruplet Polychromat does not show any decrease of the Strehl ratio near or below the diffraction limit in the peripheral regions of the visual spectrum, as is the case with most apochromats.
- Due to its polychromatic correction, the 200/1600 CaF₂ Quadruplet is the first astronomical optics that exploit the full UBVRl spectral range (365nm – 1014nm) of modern electronic sensors (CCD, CMOS).
- We source the high-quality fluorite blanks with special parameters in selected quality from a certified manufacturer, which also supplies the global players of precision optical equipment with CaF₂ raw material for the production of stepper lenses for VUV photolithography.
- The surfaces of the objective lenses made of three different special optical glasses of SCHOTT® or OHARA® and CaF₂ are precision machined, a lens surface is an asphere.
- Because every fabrication can only be done with finite precision, even the latest technologies and state-of-the-art CNC precision machining processes are subject to errors. All manufacturing parameters must therefore be tolerated conscientiously.
- The required high image quality is achieved by a final system correction, which is performed by a precision optics master with decades of experience in his field.
- Thanks to a novel compensation cell, the lenses of the completely oil spaced objective (without air gaps) are held in stable position with fluctuations in temperature.
- The thermal equilibrium sets in quickly and rattling of lenses in the cell with all negative consequences is prevented.
- The objective can be adjusted precisely to the optical axis of the OTA.
- The CNC precision machining of lens cell, dew cap and telescope tube ensures the required high centering accuracy.
- Inside the OTA, a defined surface structure and a diaphragm system in combination with an antireflective coating of all internal surfaces effectively prevent the occurrence of scattered light and tube reflections.
- The over 220mm sliding dew cap, which can

Specification

Objective APQ 200/1600	Fluorite Quadruplet Polychromat
Optical design	four lens aspherical design
Coupling technique	completely oil spaced without air gaps
Mounting type	compensation cell
Cell material	high quality aluminum and stainless steel alloys
Polychromatic Strehl ratio	≥ 0.95 (365nm – 1014nm)
Maximum focal shift range	±0.006% (365nm – 1014nm)
Anti-reflection coating	Ultra-ARB R _{AVG} < 0.7% (365nm – 1014nm)
Clear aperture	200mm
Focal length	1600mm
Focal ratio	f/8
Image scale	2.149"/mm or 0.465mm/'
Resolution	0.57" (theoretical)
Magnification range	33x – 600x (exit pupil 6mm – 0.33mm)
Test protocol	optical inspection certificate
Tube assembly 200/1600	high quality aluminum and stainless steel alloys
Tube and dew cap colors	silver metallic / black metallic
Tube diameter	Ø218mm
Telescope length (dew cap and focuser)	1225mm / 1559mm (retracted / extended)
Dew cap diameter	Ø252mm
Dew cap length	361mm
Dew cap sliding range	220mm
Backfocus	320mm
Focuser	Feather Touch FTF3545
Clear diameter	Ø90.2mm (3.55")
Focusing range	114.3mm (4.5")
Lifting capacity	8.1 – 9.1kg (18 – 20lb)
Reduction ratio	10:1
360° rotatable and lockable	yes
Motorized drive as option	yes
Weight	2.7kg (6lb)
OTA APQ 200/1600 Polychromat	objective, tube assembly, dew cap, focuser
Adapter	S108 Quick Changer
Dust-covers	covers to protect the lens and tube
Weight (including focuser)	< 21kg (46.3lb)

be clamped in any position, takes into account the maximum image field diameter of the field corrector and focal reducer corrector of 3.5° each. On the dew cap the label Polychromat 200/1600, the brand logo APQ as well as the indication of origin Made in Germany are applied.

- At the end of the refractor, the Feather Touch focuser FTF3545 from Starlight Instruments is mounted with a Quick Changer with S108 dovetail.
- The Feather Touch focuser is rotatable by 360°, so that it can always be turned into the desired position. The dual-speed mechanism with coarse and fine drive has a reduction ratio of 10:1.
- The eye-catching color of the OTA stands out significantly from the general standard white and gives the APQ JENA Polychromat a unique and distinctive design with a high value of brand recognition.
- The APQ 200/1600 Fluorite Quadruplet Polychromat is a premium refractor that is predestined for all types of observations – visual and photographic.

Recommended Accessories

- Field Corrector
- Focal Reducer Corrector
- Barlow system
- Tube Rings
- Mounting Plate
- Steering Wheel
- Tube Cap
- Carrying Handle
- Quick Changer
- Change Rings
- Extension Tubes
- Adapters
- Covers